- WALL/KILN SPACING: 12" [30.5cm] SPACING BETWEEN SIDES OF KILN AND WALLS OR OTHER OBJECTS. 18" [45.7cm] IS RECOMMENDED. LEAVE AT LEAST 18" [45.7cm] BETWEEN TWO KILNS.
- 2. **AMBIENT VENTILATION:** SEE CHART TO RIGHT FOR RATINGS. TO CALCULATE REQUIREMENTS, SEE <u>hotkilns.com/calculate-kiln-room-ventilation</u>.


LID NOT SHOWN

IN THIS VIEW

- 3. **KILN VENTILATION:** L&L VENT-SURE KILN VENT RECOMMENDED FOR SAFETY AND LONGER ELEMENT LIFE. OPTIONAL CONTROL ALLOWS VENT TO BE TURNED ON AND OFF WITH CONTROL.
- 4. **OTHER INFO:** REFER TO INSTALLATION INSTRUCTIONS AND CAUTIONS INSTRUCTIONS FOR OTHER REQUIREMENTS AND SAFETY INFORMATION. REFER TO WIRING DIAGRAM FOR ELECTRICAL HOOKUP INFORMATION.
- 5. MAX LOAD WEIGHT: SEE hotkilns.com/load-weight.
- 6. **WEIGHT OF KILN**: 885 LBS, 401 KG

BTUS/ KILOJOULES PER HOUR NEEDED TO BE VENTED WITH AMBIENT ROOM VENTILATION (THIS IS IN ADDITION TO KILN VENTING):

	·		- 1 -
AT TEMP F	BTUS	AT TEMP C	KILOJOULES
1800F	21623	980C	22814
2000F	25279	1095C	26671
2232F	29849	1222C	31493
2350F	32307	1285C	34086
	1800F 2000F 2232F	1800F 21623 2000F 25279 2232F 29849	1800F 21623 980C 2000F 25279 1095C 2232F 29849 1222C



VIEW SCALE - 1:18

