- 1. WALL/KILN SPACING: 12" [30.5cm] SPACING BETWEEN SIDES OF KILN AND WALLS 4. OR OTHER OBJECTS. 18" [45.7cm] IS RECOMMENDED. LEAVE AT LEAST 18" [45.7cm] BETWEEN TWO KILNS.
- 2. AMBIENT VENTILATION: SEE CHART TO RIGHT FOR RATINGS. TO CALCULATE REQUIREMENTS, SEE hotkilns.com/calculate-kiln-room-ventilation.
- 3. KILN VENTILATION: L&L VENT-SURE KILN VENT RECOMMENDED FOR SAFETY AND LONGER ELEMENT LIFE. OPTIONAL CONTROL ALLOWS VENT TO BE TURNED ON AND OFF WITH CONTROL.


OTHER INFO: REFER TO INSTALLATION INSTRUCTIONS AND CAUTIONS INSTRUCTIONS FOR OTHER REQUIREMENTS AND SAFETY INFORMATION. REFER TO WIRING DIAGRAM FOR ELECTRICAL HOOKUP INFORMATION.

MAX LOAD WEIGHT: SEE hotkilns.com/load-weight. 5.

WEIGHT OF KILN: 590 LBS, 268 KG



| AT TEMP F | BTUS  | AT TEMP C | KILOJOULES |
|-----------|-------|-----------|------------|
| 1800F     | 22497 | 980C      | 23735      |
| 2000F     | 26298 | 1095C     | 27746      |
| 2232F     | 31050 | 1222C     | 32760      |
| 2350F     | 33606 | 1285C     | 35456      |



5

3

2

0

235-000-60-5

